

PFA coated press arm/scattering hand

TERADA

Easy for removing stuck tea, hygienic & improvement of yield!

GAP compliant item

GAP : Good Agricultural Practice

■ Press arm spatula



■ Scattering hand



■ Bar of scattering hand



For the primary tea rolling process Terada has developed & supplied PTFE slates as a solution for tea sticking. We suggest PFA coated press arm & scattering hand for further support to cleaning, aiming improvement in aspect of hygiene.

- PFA is polytetrafluoroethylene official name of tetrafluoroethylene resin. It is high heat-resistant (260℃)、non-sticky, wear resistant and excellent anticorrosive fluororesin.
- Since PFA is coated in special method, it cannot be repaired by spraying or painting in case of peeling off. In that case it should be coated once again.

※Contact us if you want to coat the press arm and scattering hand you have.

※Part of the specifications might be changed for improvement.

TERADA 株式会社 寺田製作所
TERADA SEISAKUSHO CO.,LTD.

No.869-1 Ushio Shimada-shi Shizuoka-ken 428-8502 Japan
Phone : +81-547-45-5111 Fax : +81-547-45-5110
<https://www.web-terada.jp> E-mail: info@web-terada.jp

● Sales agent

